# **MODEL 644B-37**

**SPECIFICATIONS** 

1360 1810 2720

3000 LBS / 15000 LBS / 16000 L

5

#### **ENGINES:**

- JOHN DEERE 4039D 80 HP @ 2500 RPM
- JOHN DEERE 4045T 100 & 115 HP @ 2500 RPM
- · CUMMINS 4B3.9 76 HP @ 2500 RPM
- CUMMINS 4BT3.9 110 HP @ 2500 RPM

#### TRANSMISSION:

- 3-SPEED POWER SHIFT, FWD. & REV.
- · COLUMN-MOUNTED SHIFT LEVER
- NEUTRAL START SWITCH
- H.D. TRANSMISSION OIL COOLER
- DECLUTCH SWITCH ALLOWS BRAKE PEDAL TO DISENGAGE TRANSMISSION WHEN BRAKE IS APPLIED

#### **AXLES:**

- OUTBOARD PLANETARY WITH DOUBLE REDUCTION
- 4-WHEEL DRIVE
- LIMITED SLIP FRONT DIFFERENTIAL
- STEERING 3 MODES: 4 WHEEL ROUND,
- 2 WHEEL FRONT, AND 4 WHEEL CRAB
- HYDRAULIC FULL POWER STEERING WITH 2 DOUBLE-ACTING STEER CYLINDERS PER AXLE

### **BRAKES:**

- · 4-WHEEL, FULLY ENCLOSED, WET DISC
- HYDRAULIC ACCUMULATOR STORED ENERGY BRAKING FOR DEAD ENGINE STOPS
- "FAIL-SAFE" PARK BRAKE: SPRING APPLIED HYDRAULIC RELEASE
- DASH-MOUNTED INDICATOR LIGHTS

## **ELECTRICAL SYSTEM:**

- 12 VOLT, NEGATIVE GROUND
- 925 AMP COLD CRANKING, MAINTENANCE FREE BATTERY
- 65 AMP H.D. ALTERNATOR
- CIRCUIT BREAKER PROTECTED SYSTEM

### **FILTRATION:**

- AIR CLEANER 2 STAGE DRY TYPE WITH REPLACEABLE ELEMENTS. (VISUAL SERVICE IND. STD.)
- ENGINE OIL LUBE FULL FLOW SPIN-ON CARTRIDGE TYPE WITH BYPASS
- · FUEL FILTER WITH WATER SEPARATOR & DRAIN.
- TRANSMISSION SPIN-ON TYPE WITH SAFETY BYPASS
- MAIN HYDRAULICS 10 MICRON FULL FLOW FILTER **ELEMENT WITH SAFETY BYPASS**

# HYDRAULIC SYSTEM:

- 2-SECTION GEAR PUMP: 18 GPM TO MAIN HYDRAULICS, 18 GPM TO STEERING, BRAKE PRIORITIES
- AND HYDRAULIC SYSTEM. EXTRA FINE METERING & SELF CENTERING HYDRAULIC CONTROL VALVES.

# STANDARD EQUIPMENT:

- SEAT BELT
- HORN
- REVERSE WARNING ALARM
- NEUTRAL START SWITCH
- SKID RESISTANT FLOOR MATERIAL
- RIGHT SIDE REAR VIEW MIRROR
- ANTI-FREEZE PROTECTION TO 30°F
- MACHINE LEVEL INDICATOR

# Authorized Representative:

Lull reserves the right to make improvements in design and changes in specifications without notice and without incurring obligation as to units already sold.

© Copyright 1994 Lull International, Inc. All Rights Reserved 12/95-10M

# FUEL GAUGE, WATER TEMP. GAUGE,

HOUR METER, OIL PRESSURE GAUGE, TRANS. OIL TEMP. GAUGE, VOLT METER, PARK BRAKE APPLIED LIGHT. LOW BRAKE PRESSURE LIGHT, TRANS. DECLUTCH LIGHT 25 15

AUTOMATIC FORK LEVELING

• HYD/HYD. JOYSTICK CONTROLS (PILOT OPERATED)

STANDARD EQUIPMENT (cont'd):

• FULL INSTRUMENTATION INCLUDING:

- 2-SECTION "FULL" HYDRAULIC SLIDE BOOM
- FIRST AUXILIARY HYDRAULICS TO **BOOM TIP**
- FRAME LEVELING 12-1/2° L & R
- TIE DOWN LUGS
- 13:00 X 24 10 PLY TIRES
- QUICK ATTACH
- REAR AXLE STABILIZER SYSTEM
- OPERATOR'S COMPARTMENT ROPS/FOPS
- CONFORMS WITH ANSI/ASME B56.6,1992

# **OPTIONAL EQUIPMENT:**

• 50.5" FORK CARRIAGE

CAPACITIES SHOWN DEPICT FULL BOOM EXTENSION PRIOR TO TRANSACTION

- 50.5" SIDE TILTING CARRIAGE (10° R-L)
- DUAL FORK POSITIONING CARRIAGES AVAILABLE IN WIDTHS 50.5" OR 74"
- 74" STANDARD FRAMERS CARRIAGE
- 74" SIDE TILTING FRAMERS CARRIAGE (10° R-L)
- 2" X 4" 42"/48"/60" FORKS
- 1-3/4" X 6" 48"/60" LUMBER FORKS
- 2" X 2" CUBING FORKS ORDER IN PAIRS
- AUXILIARY HYDRAULICS FOR SECOND ACCESSORY
- 1.25 CU YD BUCKET (LIGHT MATERIAL)
- 4,500 LB CAPACITY HYDRAULIC WINCH, BOOM MOUNTED
- CAB ENCLOSURE
- HEATER/DEFROSTER
- AIR CONDITIONING
- 10' TRUSS BOOM (W/WO 2,000 LB CAP. HYDRAULIC OPERATED WINCH)
- ROADWAY LIGHT PACKAGE
- WORK LIGHT PACKAGES
- 3/4 CU YD HYDRAULIC OPERATED CONCRETE HOPPER

### OPERATING SPECIFICATIONS:

OI EILMING OF EON TOMITORIO	
LIFT AND CARRY CAPACITY	6,000 LBS
MAX. LIFT HEIGHT	37'
MAX. "LANDING HEIGHT"	
TRANSACTION	80"
MAX. HORIZONTAL FORWARD REACH	27'
MAX. REACH @ MAX. LIFT	8'
CAPACITY @ MAX. REACH	1,000 LBS
BELOW GRADE	16"
OUTSIDE TURNING RADIUS	13' 8"
GROUND CLEARANCE	
OVERALL HEIGHT	95"
OVERALL WIDTH	
OVERALL LENGTH	
WHEELBASE	124"
WEIGHT	

# CAPACITIES:

FUEL	40 GAL.
COOLING SYSTEM	18 QTS.
CRANK CASE W/ FILTER	14 QTS
HYDRAULIC RESERVOIR	44 GAL.
BATTERY	12 VOLT 925 CCA



3045 Highway 13, St. Paul, MN 55121