

## Auger Feed Hopper, Stainless Steel

Mfg:

Model:

Stock No. CCFP066A

Serial No.

Auger Feed Hopper. Stainless steel. Hopper: 26 cu. ft. Auger screw diameter: 5 in. Auger housing diameter: 5-1/2 in. Auger length: 64 in. Baldor High-Efficiency Motor: 3 hp, 1725 rpm, 208-230/460 V, 8.5-8.2/4.1 amps, 60 Hz, 3 phase. Falk Ultramite Motor Drive: 11.44 ratio, 150.78 rpm (output). Overall dimensions: 91 in. L x 42 in. W x 42-1/2 in. H.



