

## Paddle Blender 40 Cubic Feet

Mfg:

Model:

Stock No. CCIS001

Serial No.

### Paddle Blender 40 cubic feet.

- Boston Reductor Gear Works. Cat No. AT38, S/N 44113, Ratio 40-1, .71hp, 1,300/1,200 rpm.
- Dayton Motor, Model 2N935L, 2.0 hp, 3 phase, Nema design B, 184 frame, 1,760 rpm, 60 hz, 10SF, Insul Class A, Motor Ref. GO03A/C90To41004F.
- Duty: Cont. max AMB 40 ° C. Max KVAR 0.7.
- Shaft end BRG 6206, 208-220/440 volt, 6.4-6.2-3.1 amps.
- The paddle blender has a square outlet that can be opened and closed manually; it is 5-½ in. by 5-½ in.
- Inside dimensions: 26 in. W, 94 in. L, 26 in. H.
- Overall dimensions: 34 in. W, 115 in. L, 56 in. H.

