

Stainless Steel Tank with Perma-San Mixer- 40 Gallon

Mfg:

Model:

Stock No: CFPH206.8a

Serial No:

Stainless Steel Tank with Perma-San Mixer. Approximate capacity: 40 gallons. Inside straight-wall dimensions: 20 in. dia. x 2 ft. 6 in. H. Perma-San mixer, Model: PGS-4A, S/N: 3956, propeller diameter: 8 in. Reliance electric motor, 3/4 hp, 1725 rpm, 208-230/460-480 V, 2.9-2.6/1.3-1.5 amps, 60 Hz, 3 phase. Foxboro pneumatic liquid level transmitter, S/N: 2362647, Type: 17FES, range: 0-32.10 in. H₂O, diaphragm: 316 SS, maximum working pressure: 100 psi. Inlets: (2) 2 in. dia. ports, (1) 1 ft. 8 in. dia. infeed. Outlets: (1) 2 in. dia. port, (1) 2-1/2 in. dia. port. Overall dimensions: 3 ft. L x 2 ft. 9-1/2 in. W x 5 ft. 10 in. H.





