

APV Crepaco HTST

Mfg: APV Crepaco

Model: SR35

Stock No. CFPH359.41a

Serial No. 76827

APV Crepaco HTST. Model: SR35. S/N: 76827. Nat'l Bd: 3067. W.O: 21308-1. Number of plates: 148. Heat transfer surface area: approx. 632 sq. ft. Number of dividers: 1. MAWP: 150 psig @ 275°F. MDMT: 5°F @ 150 psig. Bell & Gossett Shell & Tube Heat Exchanger, S/N: 89R7762-01-4, Nat'l Bd: 9213, shell side MAWP: 150 psi @ 375°F, shell side MDMT: -20°F @ 150 psi, tube side MAWP: 125 psi @ 375°F, tube side MDMT: -20°F @ 125 psi. Centrifugal Pump, S/N: 1527422 D.8. U.S. Electric Motor, 3 hp, 1750 rpm, 230/460 V, 9.0-4.5/10.5-5.25 amps, 60 Hz, 3 phase. Condensate Tank- 13 Gallon, inside straight-wall dimensions: 1 ft. dia. x 2 ft. 4 in. L. Fisher Pneumatic Valve Positioner, S/N: 11184269, Actuator type: 667, max. supply: 90 psi, operating range: 3-15 psi, Body type: ED, material: iron, size: 3, seat: 416 sst, stem plug: 316 sst/ 416 sst, rating: CL125. (3) Stainless Steel Pneumatic Valves. Hartel Stainless Steel Control Panel, dimensions: 2 ft 6 in. L x 1 ft. W x 3 ft. H. Inlets: (2) 2 in. dia. ports, (1) 3 in. dia. port, (1) 2 in. dia. I-line fitting, (1) 2 in. dia. flanged port. Outlets: (2) 4 in. dia. flanged ports, (1) 1-1/2 in. dia. port, (2) 3 in. dia. ports, (1) 2 in. dia. flanged port. Overall dimensions: 8 ft. 7 in. L x 5 ft. 8 in. W x 11 ft. 2-1/2 in. H.















