

Mycom 6 Cylinder 2-stage Compound Reciprocating Compressor – 75 HP

Mfg: Mycom

Model: N42WB

Stock No.: CNPR001

Serial No.: 640175

Mycom 6 Cylinder 2-stage Compound Reciprocating Compressor – 75 HP. Model: N42WB. S/N: 640175. Refrigerant: Last used with R-717. Leak (psig) hi/lo: 313/185. Hydrostatic (psig) hi/lo: 470. (4) cylinders low stage and (2) cylinders high stage. Displacement: 224 cfm low stage and 112 cfm high stage at maximum rpm of 1,200. Safety device switches: oil pressure cutout, cylinder unload switch, adjustable crank heater: 60°F - 250°F, high pressure cutout switch, auxiliary oil filter, water cooled oil coolers & high temperature cutout switches. Water cooled. Great for low temperature applications. Drive pulley diameter: 1 ft.-1/2 in. Driven pulley diameter: 1 ft. 4-1/2 in. dia. Pulley ratio: 0.75. Oil capacity: 6.81 gallons. Inlets: (1) 2-1/2 in. dia. compressor suction port. Outlets: (1) 2 in. dia. refrigerant discharge port. Baldor Industrial motor, 75 hp, 1760 rpm, 230/460 V, 60 Hz, 186/93 amps, 3 ph, Series: 1196C, Frame: 365TC. Rebuilt in the summer of 2004. Overall dimensions: 4 ft. 5 in. L x 4 ft. W x 6 ft. 8 in. H. (ACN312a-BC/Motor).



