

Screw Auger Feeder with Hopper - Approx. 5.5 Cu Ft.

Mfg:

Model:

Stock No. CJR1816

Serial No.

Screw Auger Feeder with Hopper- Approx. 5.5 Cu Ft. Screw auger dimensions: 11-1/2 in. dia. x 51 in. L. Infeed hopper dimensions: 41 in. L x 21 in. W. Sumitomo SM Beier Variator Variable Speed Drive, Model No. HFAMN2-1845-2, S/N 007499C, speed range: 0.2-0.8, ratio: 17. Inlets: (1) 2 in. dia. S-line fitting, (1) 24 in. L x 12 in. W infeed. Outlets: (1) 12 in. dia. flanged discharge. Overall dimensions: 99 in. L x 21-1/2 in. W x 37 in. H.



