

Tri Clover C-series Sanitary Centrifugal Pump

Mfg: Tri Clover

Model: C216MD21T15479

Stock No. CSWB001.

Serial No. 8091

Tri Clover Sanitary Centrifugal Pump. Model: C216MD21T15479. S/N: 8091. Capacity: 105 gpm @ 166 head feet (72 psi using specific gravity of water = 1). Impeller diameter: 6 in. Seal Option: single mechanical (standard). Hawker Siddeley Electric Motor, 7 ½ hp, 3450 rpm, 575 V, 7.7 amps, 60 Hz, 3 phase. The C Series pump is the original, all-purpose, sanitary process centrifugal pump. Its practical design and flexibility have provided processors with strong performances in thousands of applications. A great value, the C-series pump maintains an integral Clean-In-Place design as standard. Inlet: (1) 2 in. dia. S-line. Outlet: (1) 1 ½ in. dia. S-line. Overall dimensions: 2 ft. 1 in. L x 1 ft. W x 1 ft. 3 in. H.



