

2004 Rockwell Automation/Allen Bradley Variable Frequency Drive – 2HP

Mfg: Rockwell Automation/Allen Bradley

Model: Powerflex 700

Stock No.: DLEC136.2a

Serial No.: 1JAYCX7

2004 Rockwell Automation / Allen Bradley Variable Frequency Drive – 2 HP. Model: Powerflex 700. Normal Duty Power: 2 hp. Heavy Duty Power: 1.5 hp. Unit is contained in a painted steel enclosure. Powerflex drives provide open or closed loop speed regulation, fast update times of torque inputs and tight torque regulation information for applications like extruders and web processes. Overall dimensions: 1 ft. 8 in. L x 11 in. W x 1 ft. 8 in. H. (ACN24).

Powerflex 700

S/N: 1JAYCX7. Catalog No. 20BD3P4A3AYNADB0. Input AC voltage range: 432 to 528, 3 Ph, 47 to 63 Hz, 2.6 amps. Output AC voltage range: 0 to 460 V, 60 Hz, 3.4 cont. amps, 4.5 amps 1 min, 6 amps 3 secs. LCD display with full numeric keypad. Brake IGBT installed without drive mounted brake resistor. DeviceNET-DPI internal communication module. Standard control with 120V I/O.



