

APV Stainless Steel Feeding Hopper Tank with Pumps-60 Gallon

Mfg: APV

Model:

Stock No.: DNBA037

Serial No.:

APV Stainless Steel Feeding Hopper Tank with Pumps - 60 Gallon. Infeed-hopper dimensions: 4 ft. 1 in. L x 2 ft. 7 in. W x 2 ft. H. (2) APV Crepaco positive displacement pumps. Model: R3R1RH. S/N's: P-9400-0788, P-9401-0798. Leeson electric motor, 1 hp, 1140 rpm, 208-230/460 V, 4-4/2 amps, 60 Hz, 3 phase. Nord gear speed reducer, ratio: 64.80, rpm out: 17 (final). Inlets: (1) 4 ft. 1 in. L x 2 ft. 7 in. W. (hopper infeed), (2) 4 in. L x 1-1/2 in. W. (pump inlets). Outlets: (2) 2 in. dia. ACME fittings. Overall dimensions: 4 ft. 1 in. L x 3 ft. W x 4 ft. H.



