

Cleated Incline Conveyor

Mfg:

Model:

Stock No. DSBI122.2a

Serial No.

Cleated Incline Conveyor. Belt width: 16 in. Cleat pitch: 14 in. W x 5 in. H. Height at conveyor inlet: 30 in. Height at conveyor outlet: 90 in. Conveyor moves on (4) casters for easy positioning. Motor, no nameplate information. Baldor Industrial Motor Drive: 40 ratio, 0.674 max hp (input), 1750 rpm (input), 680 in-lbs torque. Inlets/outlets: (1) 16 in. L x 14 in. W infeed, (1) 14 in. L x 7 in. W outlet chute. Overall dimensions: 13 ft. 3 in. L x 36 in. W x 94 in. H. Heat and Control Inc. Control Panel. Controls consist of an adjustable speed knob, emergency stop switch, and incline conveyor hand/off/auto switch. Overall dimensions: 24 in. L x 12 in. W x 31 in. H.



Click here for video file.

<http://www.food-processing-equipment.biz/images/Cleated Incline Conveyor.mov>

