

Hobart Stainless Steel Blender

Mfg: Hobart

Model: BL-20

Stock No. DSBI090.34

Serial No.

Hobart Blender. Model: BL-20. 316 stainless steel. Max/min capacity: 66/58 cu ft. Weight capacity: 2000 lbs. Blender features dual 25 in. dia. x 60 in. L paddle blender shafts and 9 in. dia. x 60 in. L screw auger in 9-1/2 in. dia. housing. Inlets/outlets: (1) 60 in. L x 48 in. W infeed opening, (1) 11 in. dia. side discharge outlet with pneumatic closing lid. Elektrim Motor: 15 hp, 1755 rpm, 230/460 V, 60 Hz, 3 phase. Motor drive, no nameplate information. Overall dimensions: 95 in. L x 52 in. W x 80 in. H.

