

Dino Vertical Multi-Pasta Processor System

Mfg: Dino

Model: JMR-92

Stock No. DSBI092.5a

Serial No. 284

Dino Vertical Multi-Pasta Processor System. Model: JMR-92. S/N: 284. 316 stainless steel. Hopper: 33-1/2 in. L x 33-1/2 in. W. Lid: 38 in. L x 34-1/2 in. W; removable, hinged. Primary processing is accomplished by a vertical screw auger. Primary screw auger: 15 in. dia. x 12 in. H. Second stage processing screw auger: 4 in. dia. x 29 in. L; 4-1/4 in. dia. housing. Side scrapers: (8) 3-1/2 in. L x 3-1/2 in. W. AC Tech variable speed drive. Sew Eurodrive Motor: 7.5 hp, 1720 rpm, 230/460 V, 19.2/9.0 amps, 60 Hz, 3 phase. Sew Eurodrive Motor Drive: 5.95 ratio, 1720 rpm (input), 289 rpm (output), 1630 lb-in. torque. Inlets/outlets: (1) 4-1/2 in. dia. side outlet, (1) 33-1/2 in. L x 33-1/2 in. W inlet. AC Tech Variable Speed Drive. Model: Q22008CX-498, S/N: 27433-305, Manual No: 1001.008X. 10.5/8.8 kVa, 240-230 V, 25.2/22 amps, 50-60/120 Hz, 3 phase. Overall dimensions: 53 in. L x 36 in. W x 66 in. H.



