

2000 E.L. Nickell Ammonia Subcooler

Mfg: E.L. Nickell

Model:






Stock No. DTTC004B.

Serial No. S008669

2000 E.L. Nickel Ammonia Subcooler. S/N: S008669. Nat'l Bd: 47629. Job No: C-14191-B. MAWP: 250 psi @ 225 °F. MDMT: -20 °F @ 250 psi. Tube material: 304 stainless steel. Number of passes: 4. Number of tubes: 460. Tube dimensions: 9/16 in. dia. x 8 ft. L. Heat transfer surface area: approx. 542 sq. ft. Tube volume: 47 gal. (4) Cyrus Shank Pressure Relief Valves, Types: 804 and 804TH*, inlet: 3/4 in., set pressure: 250 psig, air capacity: 880 and 791* scfm. Inlets: (1) 10 in. dia. port. Outlets: (3) 6 in. dia. ports. Overall dimensions: 14 ft. 10 in. L x 48 in. W x 98 in. H.







Note: the following picture show the exact unit prior to removal.

