

DINO Machinery Corporation Multi-Pasta Processor System

Mfg: DINO Machinery Corporation

Model: MKF-3000

Stock No: DSBI100.17

Serial No: 292

DINO Machinery Corporation Multi-Pasta Processor System. Model: MKF-3000. S/N: 292. Material of construction: 316 stainless steel. Approximate blender capacity: 1.15 cu ft. Blender: (6) 8 in. dia. x 1 ft. 2 in. L paddles. Screw auger, dimensions: (1) 2 in. dia. x 1 ft. 2 in. L. Hopper inlet / outlet: 7 in. dia. x 1 ft. 9 in. L / 1 ft. 9 in. W x 2-1/2 in. H. Drive units: Baldor industrial motor, 10 hp, 1725 rpm, 208-230/460 V, 30-28/14 amps, 60 Hz, 3 phase. Sumitomo SM-CYCLO motor drive: 87:1 ratio, 1750 rpm (input), 19.82 rpm (output). Sew Eurodrive motor, 7.5 hp, 1720 rpm, 230/460 V, 19.2/9.6 amps, 60 Hz, 3 phase. Sew Eurodrive motor, 5 hp, 1660 rpm, 230/460 V, 13.6/6.8 amps, 60 Hz, 3 phase. Sew Eurodrive motor drive, 5.30 ratio, 1660 rpm (input), 285 rpm (output), 1110 lb-in. Sew Eurodrive motor, 1 hp, 1700 rpm, 230/460 V, 3.9/1.98 amps, 60 Hz, 3 phase. Sew Eurodrive motor drive, 5.90 ratio, 1700 rpm (input), 288 rpm (output), 220 lb-in. torque. (2) Hub City motor drives. Telemecanique limit switches. Inlets/outlets: (2) 1-1/2 in. dia. Q-line fittings, (2) 2 in. dia. Q-line fittings, (1) 3 in. dia. Q-line fitting. Overall dimensions: 8 ft. L x 5 ft. 8 in. W x 7 ft. 4 in. H.





