

## Sumitomo SM-Cyclo Inline Drive

Mfg: Sumitomo

Model:

Stock No. DTTC2104.

Serial No.:

Sumitomo SM-Cyclo Inline Drive. Shaft diameter: 3-9/16 in. Number of sprockets: 2. Sprocket diameter: 1 ft. Number of teeth: 36. Pitch: 1 in. Baldor Electric Motor, 5 hp, 1750 rpm, 208-230/460 V, 13.8-13.4 /6.7 amps, 60 Hz, 3 phase. Overall dimensions: 3 ft. 8 in. L x 1 ft. 8-1/2 in. W x 1 ft. 5-1/2 in. H.



