

1993 FES 775 / Mycom 320SU Rotary Screw Compressor Package Less Motor

Mfg: FES / Mycom

Model: 775 / 320SU

Stock No: DTTC2066

Serial No: 3251462

1993 FES 775 / Mycom 320SU Rotary Screw Compressor Package. Model: 775 / 320SU. S/N: 3251462. FES Contract No: 93147033. Refrigerant R-717. Mycom rotary screw compressor, Model: 320SU. S/N: 3251462. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Vi setting: 3.6. Displacement: 2,236 cfm. Nominal capacity: 825 tons at 936.2 bhp with a 95°F condensing temperature and a 20°F suction temperature. 1993 FES oil separator, S/N: 930198, Nat'l Bd: 6426, MAWP: 250psi at 200°F, MDMT: -20°F at 250 psi. FES Micro II E control panel. Viking rotary positive displacement pump, P/N: 3-551-002-340. Baldor electric motor: 10 Hp, 1760 rpm, 208- 230/460 V, 28.5-28.4/14.2 amps, 60 Hz, 3 phase. U.S. Petroleum Industrial Inc. oil filtration system. Model: 1000AMM Dual. S/N: 3251462. Housing diameter: 7 in. Filter system dimensions: 2 ft. 6 in. L x 1 ft. 4 in. W x 3 ft. 10 in. H. Inlet: (1) 10 in. dia. flanged port. Outlet: (1) 6 in. dia. port. Overall dimensions: 16 ft. 1 in. L x 5 ft. 9 in. W x 10 ft. H. Approximate shipping weight: 18,600 lbs. Compressor run time: 31,119.6 hrs. since Mycom rebuild.





