

## FES 775 / Mycom 320 SU-LX Rotary Screw Compressor Package - 250 HP

Mfg: FES / Mycom

Model: 775 / 320 SU-LX

Stock No: DTTC806.

Serial No: 3251350

FES 775 / Mycom 320 SU-LX Rotary Screw Compressor Package. Model: 775 / 320 SU-LX. S/N: 3251350. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Suction pressure: 12 in. Hg @ -45°F. Discharge pressure: 33 psi @ 20 °F. Nominal capacity: 188.0 tons at 245.0 bhp. Bhp per ton: 1.303. Displacement: 2,230 cfm. FES oil separator, Nat'l Bd: 1367, MAWP: 250 psi. at 300 °F to -20 °F. Toshiba motor, 250 hp, 3540 rpm, 2300/4160 V, 58/32 amps, 60 Hz, 3 phase. Viking rotary pump, Model: AK 4195, S/N: 50. Motor, 7 hp, 1170 rpm, 230/460 V, 2.2/1.1 amps, 60 Hz, 3 phase. Mycom Mypro-M control panel. Inlet: (1) 16 in. dia flanged ammonia port. Outlet: (1) 4 in. dia. discharge. Overall dimensions: 15 ft. 4 in. L x 4 ft. 11 in. W x 7 ft. 4 in. H. (ACN1450)





-20 °F MIN. ALLOW. WORK TEMP.  
 N.A. P.S.I. MAX. A.W.R. AT MIN. TEMP.  
 PER UCS-66 [C] [2]  
 YEAR 1982 F.E.S. NO. 81281  
 MANUFACTURED BY -  
 FREEZING EQUIPMENT SALES, INC.  
 YORK, PA. U.S.A.  
 D.L. 2-1 HD. 315 TR. 315

NATIONAL BOARD  
 U 1367  
 W 250 P.S.I. MAX. W.P.  
 300 DEG. F. MAX. TEMP.  
 -20 °F MIN. ALLOW. WORK TEMP.  
 N.A. P.S.I. MAX. A.W.R. AT MIN. TEMP.  
 PER UCS-66 [C] [2]  
 YEAR 1982 F.E.S. NO. 81281





