

FES 775B / 320 SU Mycom Booster Rotary Screw Compressor Package - 300 HP

Mfg: FES / Mycom

Model: 775B / 320 SU

Stock No: DTTC809

Serial No: 3251306

FES 775B / Mycom 320SU Booster Rotary Screw Compressor Package. Model: 320 SU. S/N: 3251306. Mycom rotary screw compressor, Model: 320 SU, S/N: 3251306. Vi setting: 2.6. Displacement: 2,230 cfm. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Nominal capacity: 188 tons at 245 bhp with a -45°F suction temperature and a 20 °F discharge temperature. Brake hp per ton: 1.303. FES oil separator, S/N: 900529, MAWP: 250 psi at 200 °F, MDMT: -20 °F at 250 psi. Reliance Electric motor, 250 hp, 3569 rpm, 2300/4000 V, 67./38.5 amps, 60 Hz, 3 phase. GEA FES Micro II control panel, Viking pump, Model: AL4195, S/N: 11065680. Toshiba motor, 7-1/2 hp, 1170 rpm, 230/460 V, 22.2/11.1 amps, 60 Hz, 3 phase. Inlets: (1) 16 in. dia. flange. Outlets: (1) 4 in. dia. ammonia port. Compressor run time: 37,218 hrs since Mycom rebuild. Overall dimensions: 14 ft. 4 in. L x 4 ft. 2 in. W x 7 ft. 11 in. H. (SR400) (ACN1450).













