

Mycom 250SU-M Screw Compressor Package - 575 HP

Mfg: FES/Mycom

Model: 250SU-M

Stock No.: DTTC813

Serial No.: 2551195

Mycom 250SU-M Screw Compressor Package. Model: 250SU-M. S/N: 2551195. Last used with R-717 producing 398.2 tons at 464.3 bhp. Brake hp per ton: 1.165. Maximum speed: 3550 rpm. Displacement: 1,110 cfm. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Suction pressure: 33 psi @ 20°F. Discharge pressure: 180 psi @ 95 °F. E.L. Nickell Co. oil separator, MAWP: 250 psi., Maximum temperature: 650°F, Minimum temperature: -20°F. General Electric motor, 575 hp, 3575 rpm, 2400/4160 V, 107/62 amps, 60 Hz, 3 phase. Viking rotary pump, Model: AK 4195, S/N: 1157955. Baldor motor, 5 hp, 1160 amps, 208-230/460 V, 11-18.8/7.5 amps, 60 Hz, 3 phase. Mycom Mypro-M controller, 460 V Inlets: (1) 12 in. dia. ammonia flange. Outlets: (1) 4 in. dia. port. Overall dimensions: 13 ft. L x 4 ft. 10 in. W x 7 ft. 8 in. H.(ACN845)CF.









