

# FES 575 ME / Mycom 250L Ammonia Screw Compressor Package - 700 HP

Mfg: FES Mycom

Model: 575 ME / 250L

Stock No.: DTTC836

Serial No.: 2512535

FES 575 ME / Mycom 250L Ammonia Screw Compressor Package - 700 HP. Model: 575 ME / 250L. S/N: 2512535. FES Oil Separator, S/N: 87105, Nat'l Bd: 2927, MAWP: 250 psi, maximum temperature: 200 °F. Viking rotary pump, Model: AL4195, S/N: 11677690. Reliance Electric motor, 7.5 hp, 1175 rpm, 230/460 V, 20/10 amps, 60 Hz, 3 phase. FES Micro II control panel. Baldor Industrial motor, 700 hp, 3575 rpm, 2300/4160 V, 152/84 FLA, 60 Hz, 3 phase. Inlets: (1) 13-1/2 in. dia. suction port with a 17 in. flange. Outlets: (1) 5 in. dia. discharge port. Overall dimensions: 13 ft. 9 in. L x 4 ft. 10 in. W x 9 ft. 2 in. H. Compressor run time: 39,536 hrs. (SR350) (ACN950).













