

Mycom 250SU-MX Screw Compressor Package - 575 HP

Mfg: Mycom

Model: 250SU-MX

Stock No.: DTTC814

Serial No.: 2552818

Mycom 250SU-MX Screw Compressor Package. Model: 250SU-MX. S/N: 2552818. Last used with R-717 producing 398.2 TR at 464.3 bhp. Brake hp per ton: 1.165. Vi setting: 3.8. Displacement: 1,110 cfm. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Suction pressure: 33 psi @ 20°F. Discharge pressure: 180 psi @ 95°F. FES oil separator, MAWP: 250 psi, Maximum temperature: 300°F, Minimum temperature: -20°F. General Electric motor, 575 hp, 3575 rpm, 2400/4160 V, 107/62 amps, 60 Hz, 3 phase. Viking pump with motor, Model: AK1195, S/N: 10651425. Mycom Mypro-M control panel. Overall dimensions: 13 ft. 2 in. L x 4 ft. 10 in. W x 7 ft. 10 in. H. Compressor run time: 52,102 hrs.(ACN845)CF.











