

## D & W Dimple Jacket Welding Stainless Steel Tank-775 Gallon

Mfg: D & W

Model:

Stock No. DTWA401.34a

Serial No. 3944

D & W Dimple Jacket Welding Stainless Steel Tank-775 Gallon. S/N: 3944. National Board: 184. Design shell: 75 psi at 350 °F, jacket: 150 psi. Test shell: 115 psi, jacket: 115 psi. Pace Maker motor, 10 hp, 1725 rpm, 230/460 V, 24.4/12.2 amps, 60 cycles, 3 phase. Motor drive, output: 155 & 52, reducer ratio: 11.49, final rpm: 150. Temperature gauge. Mixer shaft: 2-1/2 in. diameter x 92 in. L., propeller: 30 in. L., (4) baffles. Manway: 15-3/4 in. diameter. Tank inlet: 5 in. diameter, flange: 10 in. diameter with (8) hole, center to center: 8 in. L., inlet: 2 in. diameter, flange: 8 in. diameter with (4) hole, center to center: 7 in. L., 1-1/2 in. pipe. Overall dimensions: 61 in. diameter x 16 ft. 3 in. H.



