

Graver Inner Dimpled Jacket Stainless Steel Mixing Tank-1600 Gallon

Mfg: Graver

Model:

Stock No: DTWA407.26

Serial No:

Graver Inner Dimpled Jacket Stainless Steel Mixing Tank. Estimated capacity: 1600 gallons. Jacket MAWP: 150 psi at 400 °F. Allis Chalmers motor, 7.5 hp, 1750 rpm, 230/460 V, 20.6/10.3 Amps, 60 Hz, 3 phase. Lightnin mixer information. Model no. 218-RELB-7.52 Serial no. 687184. 7.5 hp, ratio: 17.5-1, final rpm: 100. (1) 3 ft. 1 in. dia. 316 stainless steel mixer impeller. (1) Paul Mueller Company dimpled stainless steel jacket made up of (3) pieces. 1st piece info: Max W. P. 150 psi, max temp., 400 °F, serial no. 124202-1, year: 1973, Nat'l. B.D. 2143. 2nd piece info: Max W. P. 150 psi, max temp., 400 °F, serial no. 124202-2, year: 1973, Nat'l. B.D. 2144. 3rd piece info: Max W. P. 150 psi, max temp., 400 °F, serial no. 124202-3, year: 1973, Nat'l. B.D. 2145. Max height of jacket: 2 ft. 11-1/2 in. Tank inside dimensions: 5 ft. 9 in. straight wall x 6 ft. 11 in. dia. Inlet/outlet: (1) 6 in. top port, (1) 3 in. FNPT bottom port. Overall Dimensions: 7 ft. 6 in. L x 7 ft. 6 in. W x 9 ft. 2 in. H.







