

Centrifugal Heart Washer

Mfg:	Model:
Stock No. EEGC136.2a	Serial No.

Centrifugal Heart Washer. Stainless steel. Inlet: 11 in. Maximum dia. of tank: 32 in. Hydraulically operated cover plate for product removal with dimensions: 18 in. L x 10 in. W. Top tank lid secured by 4 bolts. Cover/access plates: (2) 7-1/2 in. L x 3 in. H. Outlet: (1) 4-1/2 in. dia. threaded. Motor specs: 1-1/2 hp, 3500 rpm, 220/380 V, 50 Hz, 68/39 amps, 3 phase. Overall dimensions: 36 in. L x 36 in. W x 68 in. H.

