

Raque Piston Filler Station

Mfg: Raque

Model: TP-F

Stock No. EEGC118.1a

Serial No. 0127

Raque Piston Filler Station. Model: TP-F. S/N: 0127. Capacity: ½ gallon. Filler valve: ½ in. dia. Piston: 4 in. dia. x 1 ½ in. L. Cylinder dimensions: 4 in. dia. x 9 ½ in. L. Blender inside straight wall dimensions: 3 ft. L x 1 ½ ft. W x 1 ½ ft. H. Capacity: 6.7 cu. ft. Blade dimensions: 1 ft. 4 in. L x 1 ½ in. W. Paddle dimensions: 1 ft. 5 in. L x 4 in. W. Dayton Motor Drive: ½ hp, 60 rpm (final), 208-230/460 V, 2.2/1.1 amps, 60 Hz, 3 phase, 28.6:1 ratio. Numatics Valve Model: 33JDR4410000000. Conveyor maximum aperture/clearance: 5 in. W x 4 ½ in. H. Conveyor in-feed/exit height: 3 ft. Outlet: (1) 3 in. dia. port. Overall dimensions: 7 ft. L x 3 ft. 8 in. W x 4 ft. 6 ½ in. H.







