

Scherping Welding Inc. Stainless Steel Skid Mounted 3-Tank CIP System

Mfg: Scherping Welding Inc.

Model:

Stock No: HDAF534.59a

Serial No:

Scherping Welding Inc. Stainless Steel Skid Mounted 3-Tank CIP System. (1) 100 gallon stainless steel CIP tank, straight wall dimensions: 2 ft. 6-1/8 in L x 2 ft. 9-1/8 in. W x 2 ft. 8 in H. (2) 200 gallon stainless steel CIP tanks, straight wall dimensions: 3 ft. 10-1/8 in. L x 2 ft. 9-1/8 in. W x 3 ft. 4 in. H. Ampco centrifugal pump, Model: 3 x 2-1/2 DC2, S/N: CC-19070-1-1. Flow rate for new pump is 200 gpm with required horsepower and pressure. Rpm: 3,500, Impeller diameter: 4-5/8 in. Baldor industrial motor, 7-1/2 hp, 575V, 3450 rpm, 60 Hz, 7.2 amps, 213JM frame size. Skid mounted system with a remote Panel Systems Co. stainless steel control panel, S/N: 102780. (5) pneumatic valves. Inlets: (5) 2-1/2 in S-line fittings, (2) 2 in. S-line fittings. Outlets: (2) 2-1/2 in. S-line fittings, (3) 3 in. S-line fittings (overflow tubes). Overall dimensions: 16 ft. 6 in. L x 2 ft. 10 in. W x 6 ft. 2 in. H.



















