

Custom Metal Designs 4 ft. Air Elevator Conveyor

Mfg: Custom Metal Designs

Model:

Stock No. HDCD158.3a

Serial No.:

Custom Metal Designs 4 ft. Air Elevator Conveyor. Stainless steel (2) Reliance motors, 10 hp, 1725 rpm, 208-230/460 V, 2.8-2.8/1.4 amps, 60 Hz, 3 phase. (2) Dodge Quantis motor drives, 27.97 ratio, input: 1750 maximum, output power: 1.26 hp maximum, output: 61.67 rpm. Manual adjustable clearance: 3 in. W minimum; 13 in. W maximum. Hold belt system: 1-1/2 in. L x 1-1/4 in. W x 3-1/2 in. H. Conveyor entry: 30 in. H; exit: 85 in. H. Control box: on/off switch, start, stop, run, local/remote. Overall dimensions: 10 ft. L x 53 in. W x 96 in. H.



