

Fristam Sanitary Centrifugal Pump FP Series

Mfg: Fristam

Model: FP 1722

Stock No. ENDX694.1a

Serial No. 122164009

Fristam Sanitary Centrifugal Pump FP Series. Model: FP 1722. S/N: 122164009. Capacity: 300 gpm @ 91 tdh (~40 psi using specific gravity of water = 1). Impeller diameter: 6 in. (150 mm). Least displacement per revolution: 0.086. Material of construction: 316L stainless steel. Seal option: double mechanical, Viton elastomers. Baldor Industrial Motor, 7 ½ hp, 3450 rpm, 575 V, 6.9 amps, 60 Hz, 3 phase. These heavy-duty, high performance sanitary centrifugal pumps handle the most demanding applications such as liquid withdrawal from evaporators under vacuum, viscous, hot, or abrasive products. Inlet: (1) 2-1/2 in. dia. S-line fittings. Outlet: (1) 1-1/2 in. dia. S-line fittings. Overall dimensions: 2 ft. 5 in. L x 10 in. W x 1 ft. 2 in. H. (ACN37).



