

1997 Waukesha Cherry-Burrell High Pressure Homogenizer

Mfg: Waukesha Cherry-Burrell

Model: 3000

Stock No: HDDC334.70

Serial No: 191169

1997 Waukesha Cherry Burrell High Pressure Pump. Model: 3000. S/N: 191169-97. Capacity: 2400 gph at 1800 psi. Poppet seat valves, 2 in. plungers and single-pass valve. Marathon Electric motor: 75 hp, 1775 rpm, 230/460V, 171/86a, 60 Hz, 3 phase. (1) Thermal Transfer Products heat exchanger: Model no. RM-2S. Serial no. 16102. Operating Pressure: 150 psi at 350 °F. (1) Hydraulic pump with Leeson motor: ½ hp, 1725 rpm, 115 /208-230 v, 60 Hz, 1 phase. Pulley info: (1) 9 in. driver, (1) 9-3/4 in. driven. Dodge gear box: 5.5 to 1 gear ratio. Inlets/outlets: (1) 3 in. flange, (2) 3 in. I-line, (2) ¾ in. FNPT. Overall dimensions: 4 ft. 9 in. L x 4 ft. 5 in. W x 4 ft. 11-1/2 in. H.













