

Stainless Steel Chain Conveyor

Mfg:

Model:

Stock No. ERCS018.

Serial No.:

Stainless Steel Chain Conveyor. Maximum product width: 11 in. Leeson Motor, 1.5 hp, 1725/1425 rpm, 208-260/460 V, 4.6/5.4 amps, 60/50 Hz, 3 phase. Rolls on (8) wheels for easy maneuverability. Infeed/exit height: 45-1/2 in. H. Overall dimensions: 26 ft. 4 in. L x 34 in. W x 46 in. H.

