

Cherry Burrell Farm Tank- 400 Gallon

Mfg: Cherry-Burrell

Model: FTNH

Stock No. G615-A

Serial No. 400 FTNH54 401

Cherry Burrell Farm Tank- 400 Gallon. Model: FTNH. S/N: 400 FTNH54 401. Inside dimensions 42 in. W x 81 in. L x 32 in. H. Unit is equipped with (2) 7 in. dia. manways and (2) 48 in. L x 37 in. W flip-top lids. Tank features a 26 in. dia. bottom sweep agitator rotating on a 1-1/2 in. dia. x 28 in. H shaft. Master Motor, 1/3 hp, 1725 rpm, 115/230 V, 5.6/2.8 amps, 60 Hz, single phase. Outlets: (1) 1-1/2 in. dia. port. Overall dimensions: 47 in. W x 92 in. L x 45 in. H.



