

## Modernpack Sepamatic 2000V




Mfg: Modernpack

Model: SEPA 2000V


Stock No. GAFF001.

Serial No. 195692





Modernpack Sepamatic 2000V. Model: SEPA 2000V. S/N: 195692. Contact pressure: 0-1,600 psi. Speed of perforated drum: 20-35 rpm. Electrical requirements: 12 hp, 460 V, 19 amps, 60 Hz, 3 phase. The Sepamatic is designed to press and separate pre-cut pieces of meat from sinews and gristle. Meat is fed between the belt and rotating drum. This belt separator has a filter screen with holes of 5-12 thousandths of an inch for desinewing and removing the bone particles. The bone particles are then removed by a scraper. The resultant product is equal to raw minced meat. Overall dimensions: 47 in. L x 47 in. W x 55 in. H.












**BFD CORPORATION**

**RECOMMENDED SPARE PARTS LIST**

**SEPAMATIC 2000V FOR HYDRAHOPP SYSTEM**

Revised 04/05/99 for Valley Pride Pack.

ORDERING NUMBER	DESCRIPTION	QTY	PRICE	EXT. PRICE
37.010206	BELT	3	859.79	2579.37
2000 1.3MM WOF	DRUM 1.3MM WOF	1	12888.75	12888.75
21.200.00.03604	WASHER	2	39.39	78.78
21.200.00.03704	LOCKING NUT	1	282.01	282.01
21.200.00.09803	SLIDE GUIDE	1	2219.52	2219.52
21.200.00.10802	KNIFE HOLDER	1	633.96	633.96
21.200.00.10903	AXLE	1	197.39	197.39
21.200.00.11003	KNIFE	6	64.54	387.24
21.200.W.12604	FRONT PLATE NUT SMALL	3	154.81	484.43
21.200.00.12703	FRONT PLATE NUT LARGE	2	185.22	370.44
21.200.00.14833	ECCENTRIC BOLT	2	226.22	452.44
21.200.00.17204	NUT	2	83.88	167.38
21.200.00.31504	COVER PLATE 	2	290.04	580.08
40 503.00.00138	CLAMPING ELEMENT	1	238.33	238.33
40,717.55.15119	V-BELT	1	264.60	264.60
41.205.00.06208	FRONT PLATE BEARINGS <sup>55 6208</sup>	4	174.01	696.04
43.020.34.20800	O-RING	2	21.04	42.08
51.300.12.01820	PHOTOEYE	1	182.50	182.50
51.500.00.00001	POWER MAGNET	1	126.29	126.29
51.500.00.00003	POWER MAGNET	1	79.04	79.04
21.200.00.10604	FLAT SCREW	2	51.25	102.50

23033.17

STAINLESS