

FBN Metal Products Belt Conveyor – 15 in. W

Mfg: FBN Metal Products

Model: 32-48-15

Stock No: GM420B.3

Serial No: 15825

FBN Metal Products Belt Conveyor. Model: 32-48-15. S/N: 15825. Conveyor effective length: 4 ft. Belt width: 1 ft. 3 in. Electric motor, 0.75 hp, 1725 rpm, 208-230/460 V, 3.2-3/1.5 amps, 60 Hz, 3 phase. Gear ratio: 60.1:1. Final rpm: 29. Conveyor infeed/exit height: 2 ft. 6-1/2 in. Overall dimensions: 4 ft. 2 in. L x 2 ft. W x 3 ft. 1/2 in. H.





Speed Reducer

MODEL NO 47300C

RPM OUTPUT 129 RPM INPUT 1750 GEAR RATIO 60.1
OUTPUT TORQUE 636 IN-LBS MAX INPUT HP 0.50

SF 1.0 REF NO J865/K988145N

AGMA NO 8 VISCOSITY AT 100°F 2500

FBN METAL PRODUCTS, INC.

5020 NATHANIEL LYON
BATTLEFIELD, MO 65619
800-538-2880

MODEL NO. SERIAL NO.

32-48-15 15825