

Fristam 1 hp Pump Model FPX701975H

Mfg: Fristam

Model: FPX701

Stock No. HDPH433.3

Serial No. FPX70197513

Fristam Centrifugal Pump.

- Model FPX701
- S/N FPX70197513
- Outlet 1-3/8 in.
- Inlet 1-1/2 in.
- Baldor Industrial Motor. Model CWDM3546T, 1 hp, 1,725 rpm, 484 final rpm, 208-230/460 volt, 3.5-3.2/1.6, 60 hz, 3 phase, 143TC frame.
- Overall dimensions 9 in. W x 11 in. L x 24 in. H.







FP/FPX 701 1750 RPM Inlet 1 1/2"-Outlet 1 1/2"

Performance curves based on tests using 70°F water. A tolerance of ±5% applies to all figures. For vacuum withdrawal applications contact Fristam Pumps. The smallest motor available for the FPX 701 is a 1 HP, 143TC frame.

