

SSTD LOW PROFILE COOLERS — 3 FAN MODELS

Model No.	Capacity* (Btuh/TD)		Airflow (CFM)	Velocity (FPM)	Fan Data				Coil Data			Shipping Wt. (lbs.)	Electric Defrost (KW)		
	Wet	Frosted			Motor Hp	RPM	Dia.	dBA†	Rows Deep	fpi	Volume (ft ³)		Room Temp		
													>or=-20°F <or=+5°F	>+5°F <or=+33°F	>+33°F
SSTD3-01040-3	11440	10400	17191	614	1/2	870	30	76	6	3	2.1	1498	29.5	19.3	15.4
SSTD3-01193-3	-	11930	20878	746	1	870	30	77	6	3	2.1	1494	35.4	27.9	22.4
SSTD3-01232-3	13366	12319	16219	579	1/2	870	30	76	8	3	2.8	1618	42.8	27.9	22.4
SSTD3-01242-4	13663	12421	16814	600	1/2	870	30	76	6	4	2.1	1555	35.4	27.9	22.4
SSTD3-01342-3	-	13418	25499	911	1-1/2	1160	30	83	6	3	2.1	1495	35.4	27.9	22.4
SSTD3-01371-6	15088	13717	15870	567	1/2	870	30	76	6	6	2.1	1674	35.4	27.9	22.4
SSTD3-01405-3	-	14046	19380	692	1	870	30	77	8	3	2.8	1614	42.8	27.9	22.4
SSTD3-01407-4	-	14070	20240	723	1	870	30	77	6	4	2.1	1551	35.4	27.9	22.4
SSTD3-01412-3	-	14121	27617	986	2	1160	30	84	6	3	2.1	1565	35.4	27.9	22.4
SSTD3-01426-4	15467	14255	15694	560	1/2	870	30	76	8	4	2.8	1694	42.8	27.9	22.4
SSTD3-01538-6	16693	15385	14528	519	1/2	870	30	76	8	6	2.8	1851	42.8	27.9	22.4
SSTD3-01601-3	-	16011	23805	850	1-1/2	1160	30	83	8	3	2.8	1615	42.8	27.9	22.4
SSTD3-01601-4	-	16012	24814	886	1-1/2	1160	30	83	6	4	2.1	1552	35.4	27.9	22.4
SSTD3-01632-4	-	16318	18723	669	1	870	30	77	8	4	2.8	1690	42.8	27.9	22.4
SSTD3-01673-3	-	16727	25457	909	2	1160	30	84	8	3	2.8	1685	42.8	27.9	22.4
SSTD3-01676-4	-	16760	26612	950	2	1160	30	84	6	4	2.1	1623	35.4	27.9	22.4
SSTD3-01756-6	19060	17566	17146	612	1	870	30	77	8	6	2.8	1847	42.8	27.9	22.4
SSTD3-01846-3	-	18461	29655	1059	3	1160	30	84	8	3	2.8	1761	42.8	27.9	22.4
SSTD3-01852-4	-	18524	22869	817	1-1/2	1160	30	83	8	4	2.8	1691	42.8	27.9	22.4
SSTD3-01945-4	-	19454	24428	872	2	1160	30	84	8	4	2.8	1762	42.8	27.9	22.4
SSTD3-02137-4	-	21372	28381	1014	3	1160	30	84	8	4	2.8	1838	42.8	27.9	22.4

* Capacity based on R717 refrigerant with either recirculated or flooded feed.

† Sound ratings are based on 6 feet from the unit and under free field conditions.