

Turbo Flowtube System

Mfg:

Model: MG 711/D

Stock No. HDSC126.2a

Serial No. 245095/2

Turbo Flowtube System. Model (sensor): MG 711/D. S/N: 245095/2. Electrodes: 316. Maximum flow rate: 100 gpm. Pulse rate: 1 pulse/gallon. Cx: 0.805. Turbo USP Signal Converter, S/N: 195.179. Power supply: 110 VAC. Output: 4-20 mA. Inlets/outlets: (2) 2-1/2 in. dia. ports. Overall dimensions (sensor): 11-1/2 in. L x 8 in. W x 10-1/2 in. H. Overall dimensions (transmitter): 13-1/2 in. L x 9 in. W x 16 in. H.



