

FES 95 / Dunham-Bush 1610 Rotary Screw Compressor Package - 100 HP

Mfg: FES / Dunham-Bush

Model: 95 / 1610

Stock No: HBSV002

Serial No: 5271

FES 95 / Dunham-Bush 1610 Rotary Screw Compressor Package. Model: 95 / 1610. S/N: 5271. Order No: X5271. Contract no. 96354101. Dunham-Bush rotary screw compressor, Model: 1610, S/N: 5271. Leak pressure: 313 psi. Hydrostatic pressure: 471 psi. Displacement: 278 cfm. Westinghouse motor, 100 hp, 3,545 rpm, 230/460 V, 222/111 amps, 60 Hz, 3 phase. Toshiba electric motor, 3 hp, 1155 rpm, 230/460 V, 10.0/5.0 amps, 60 Hz, 3 phase. Vi setting: 5.4. FES oil separator, S/N: 82131, Nat'l Bd: 1508, MAWP: 300 psi at 300 °F to -20 °F, head radius: 2:1, head thickness: 0.312 in., shell thickness: 0.312 in. Viking rotary pump, Model: AS4195, S/N: 10440108. Inlet: (1) 4 in. dia. suction. Outlet: (1) 2 in. dia. discharge. Compressor run time: 18,867 hours since FES rebuild in 1996. Overall dimensions: 10 ft. 10 in. L x 4 ft. 1 in. W x 8 ft. H.







