Splitcase Centrifugal Pump	
Mfg:	Model:
Stock No. HSCI005.	Serial No.

(2) Splitcase Centrifugal Pumps. Pumps are equipped with double mechanical seals. (2) Lincoln Motors, 125 hp, 1,710 rpm, 230/460V, 288/144 amps, 60 Hz, 3 phase. Inlets: (1) 10 in. dia. pipe. Outlets: (1) 8 in. dia. inlet with a 13-1/2 in. dia. flange and (8) 3/4 in. dia. holes at a center-to-center distance of 12 in. Overall dimensions of pumps: 63 in. L x 38 in. W x 34 in. H. Overall dimensions of motors: 29 in. L x 23 in. W x 20 in. H.





