

## 1990 Cleaver Brooks CB Packaged Firetube Boiler- 40 HP

Mfg: Cleaver Brooks

Model: M700-40

Stock No. HUMF001.

Serial No. L88877

1990 Cleaver Brooks CB Packaged Firetube Boiler- 40 HP. Model: M700-40. S/N: L88877. Input: 1,674,000 btu/hr. Natural gas. Steam capacity: 1380 lbs/hr @ 212 °F. Heating surface area (fireside/waterside): 200/219 sq. ft. Maximum pressure: 150 psi. Electrical requirements: 460 V, 2 amps, 60 Hz, 3 phase. Control circuit requirements: 120 V, 7 amps, 60 Hz, single phase. Cleaver Brooks Blower Motor, 1 hp, 3450 rpm, 208-230/460 V, 3.7-3.7/1.85 amps, 60 Hz, 3 phase. Inlet: 1-1/4 in. dia. male npt. Outlet: 1-3/4 in. dia. port, 7-1/2 in. dia. flanged blower exhaust. Overall dimensions: 11 ft. 6 in. L x 52 in. W x 80 in. H. Cleaver Brooks Condensate Return Tank- 100 Gallon. Tank dimensions: 24 in. dia. x 51-1/2 in. L. (2) Burks Centrifugal Pumps, S/N's: 421134 and 503979, Cat No's. 310CS5M and 310CS5M. (2) Franklin Electric Motors, 1 hp, 3450/2875 rpm, 208-230/460 V, 60/50 Hz, 3.4/1.7 amps, 3 phase. Overall dimensions (tank): 63 in. L x 28 in. W x 83 in. H. Cleaver Brooks Condensate Return Tank- 100 Gallon. Tank dimensions: 24 in. dia. x 51-1/2 in. L. (2) Burks Centrifugal Pumps, S/N's: 421134 and 503979, Cat No's. 310CS5M and 310CS5M. (2) Franklin Electric Motors, 1 hp, 3450/2875 rpm, 208-230/460 V, 60/50 Hz, 3.4/1.7 amps, 3 phase. Overall dimensions (tank): 63 in. L x 28 in. W x 83 in. H.





