

## COP Tank

Mfg:

Model:

Stock No. HDKF306.9

Serial No.

COP Tank. Stainless steel. Inside dimensions: 50 in. L x 20 in. W x 17 in. H. Forward sloping tank has 3-hook racks and 20 in. L x 18 in. W x 2 in. H basket. Ampco Centrifugal Pump, Model: 11/2X11/4 KC2, S/N: CC-20612-1-1. The Ampco line of nickel aluminum bronze centrifugal pumps are ideally suited for saltwater, as well as water, waste water and pollution control applications. Pump specifications: impeller diameter: 6.500, capacity: 65 gpm, head of feet: 23. Baldor Motor, 5 hp, 1725 rpm, 230/460 V, 13/8.5 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. suction NPT (female, pump), (1) 1-1/2 in. dia. NPT (female, tank). Outlets: (1) 1-1/4 in. dia. discharge NPT (female, pump), (1) 2 in. dia. threaded fitting (tank). Overall dimensions: 73-1/2 in. L x 25-1/2 in. W x 58 in. H.

