

## Toshiba High Efficiency Motor - 400 HP

Mfg: Toshiba

Model:

Stock No. HDKF722B.

Serial No. 93306015

Toshiba High Efficiency Motor - 400 HP. S/N: 93306015. Nominal Efficiency: 94.5%. Frame: 507USS. Maximum ambient working temp: 40°C (104°F). Continuous Duty. Motor specifications: 400 Hp, 3565 rpm, 2300/4160 V, 91/51 amps, 3 phase, 60 Hz. SNCL (Enclosure): Open Drip Proof (ODP). SP: 1.15. Bearing No: 6313C, Nema Design: B, Code: F/F. Insulation class: F, ODE: 6313C3. Overall dimensions: 3ft. 9 in. L x 2ft. 4in. in. W x 2ft.1 in. H.



