

## Screw Auger Conveyor

**Mfg:**

**Model:**

**Stock No: KWBF158B**

**Serial No:**

Screw Auger Conveyor. Auger diameter: 9-1/2 in. Pitch: 9 in. Motor, 3 hp, 1755 rpm, 230/460 V, 9.4/4.7 amps, 60 Hz, 3 phase. Falk speed reducer, model: 1115J-14A, ratio: 13.90:1, rpm out: 135 (final). Galvanized steel construction. Unit was last used as an ice auger. Inlets: (1) 2 ft. 9 in L x 10 in. W. Outlets: (1) 11 in. L x 10 in. W. Overall dimensions: 24 ft. L. x 1 ft. 2 in. W. x 1 ft. 4 in. H.





