

FES Low Temperature Ammonia Recirculating System 42 in. x 10 Ft.

Mfg: FES

Model:

Stock No. HDKF822.8

Serial No.

FES Low Temperature Ammonia Recirculating System 42 in. x 10 Ft.. Nat'l Bd: 1113. MAWP @ 300 °F: 150 psi. MDMT @ 260 psi: -50 °F. Tank diameter: 42 in. Tank length: 115 in. Insulation: 6 in. (head); 3 in. (barrel). Head radius: 2:1. Head thickness: 0.312 in. Shell thickness: 0.312 in. (2) Cornell Liquid Recirculating Centrifugal Pumps, Model: 2 CB-5-4, S/N's: 85137 and 85138. (2) Baldor Industrial Motors, 3/5 hp, 1470/1760 rpm, 190/380-230/460 V, 11/5.5-13.6/6.8 amps, 50/60 Hz, 3 phase. Inlets: (1) 6 in. dia. port, (1) 5-1/2 in. dia. port. Outlets: (1) 3 in. dia. port. Overall dimensions: 12 ft. 8 in. L x 68 in. W x 9 ft. H. Recirculating system features: 10-gallon receiving tank, FES Control Panel.



