

**1995 RVS Ammonia Recirculator Package- 39 in. Dia. x 6 ft. 10 in. H**

**Mfg: Refrigeration Valves and Systems Corporation (RVS)**

**Model:**

**Stock No: KWBF204.2**

**Serial No: 95887**

1995 RVS Ammonia Recirculator Package. Nat'l Bd: 8302. S/N: 95887. Approximate capacity: 464 gallons. Inside straight-wall dimensions: 39 in. dia. x 6 ft. 10 in. H. MAWP: 250 psi @ 300° F. MDMT: -20°F @ 250 psi. (2) 1995 Cornell ammonia centrifugal pumps, Model: 2CB-5-4, S/N's: 87333 and 87332. Impeller diameter: 10.83 in. Mechanical seal: John Crane, 1.25 in., T-1, double mechanical shaft seal with pressurized barrier fluid lubrication system, low oil limit switch, and seal chamber heater to maintain proper barrier oil viscosity. Baldor industrial motor, 3 hp, 1760 rpm, 230/460V, 13.6/6.8 amps, 60 Hz, 3 phase. Inlet: (1) 4 in. dia. port. Outlet: (1) 2 in. dia. port. Vessel inlets: (2) 4 in. dia. flanged port, (1) 1-1/2 in. dia. port. Vessel outlets: (2) 4 in. dia. port, (1) 1-1/2 in. dia. port. Overall dimensions: 5 ft. 2 in. dia. x 10 ft. 5 in. H.





















