

Dynaric Inc. DF11-SA Strapper

Mfg: Dynaric Inc

Model: DF11-SA

Stock No: KWBF342.1

Serial No: 9133

Dynaric Inc. Strapper. Model: DF11-SA. S/N: 9133. This strapper is a proven “workhorse” capable of over 37 strapping cycles per minute. It has a rugged frame and roller table top construction. Arch size: 1 ft. 3 in. W x 1 ft. 4 in. H. Tension: Adjustable with external control: 10 to 250 lbs. Cycle initiation is by start switch. Infeed/Outfeed height: 2 ft. 7-3/8 in. Power requirements: 230 V, 60 Hz, 3 phase. This machine uses 3/8 in. strap. The dispenser is internally located which minimizes the required floor space. The strapping material is heat sealed for maximum seal efficiency. Overall dimensions: 3 ft. 8-3/4 in. L x 1 ft. 1-1/2 in. W x 5 ft. 3/4 in. H.





