

2004 Statco Engineering and Fabricators, Inc. Space Saver CIP System

Mfg: Statco Engineering and Fabricators, Inc.

Model:

Stock No.: HDWR060.17a

Serial No.:

2004 Statco Engineering and Fabricators, Inc. Space Saver CIP system. Stainless Steel Inline Filter, filter dimensions: 7-1/2 in. dia. x 2 ft. 9 in. H, filter rod diameter: 1 in., filter spray gap diameter: 1/4 in. (3) Sudmo SVP Pneumatic Divert Valves. Inlets: (2) 2-1/2 in. dia. S-line fittings, (1) 1-1/2 in. dia. S-line fitting. Outlets: (2) 2-1/2 in. dia. S-line fittings. Overall dimensions: 2 ft. 11 in. L x 2 ft. 1 in. W x 4 ft. 3 in. H.

Stainless Steel Shell and Tube Heat Exchanger. Model: SCC-1236-201619. S/N: 155503. Tube material: 316 stainless steel. Number of passes: 1. Number of tubes: 120. Tube dimensions: 1/2 in. dia. x 3 ft. Heat transfer surface area: approx. 47.1 sq. ft. Approximate total tube volume: 3.6 gal. Shell side MAWP: 300 psi @ 150°F. Tube side MAWP: 300 psi @ 300°F. Inlets: (1) 2-1/2 in. dia. S-line fitting (product), (1) 3 in. dia. ACME fitting (media). Outlets: (1) 2-1/2 in. dia. S-line fitting (product), (1) 1-1/2 in. dia. NPT fitting (media). Overall dimensions: 4 ft. 10 in. L x 11 in. W x 2 ft. 3 in. H.

Fristam FT Series Sanitary Centrifugal Pump. Model: FT202-140. S/N: FT2020304583. Impeller diameter: 5-1/2 in. Baldor Washdown Motor, 10 hp, 3500 rpm, 208-230/460 V, 25-23/11.5 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. S-line fittings. Outlets: (1) 2 in. dia. S-line fittings. Overall dimensions: 2 ft. 5 in. L x 1 ft. 1 in. W x 1 ft. 3 in. H.

Stainless Steel Control Panel with AJ-300 Anderson Chart Recorder. Model: 32120110002100. S/N: 1055080-0016. Allen Bradley MicroLogix SLC 1000 Microprocessor, power supply: 115/230 VAC, 50/60 Hz, 25 amps max. Overall dimensions: 2 ft. 6 in. L x 1 ft. 1-1/2 in. W x 3 ft. H.











