

## Centrifugal Blower – 15 HP

**Mfg:**

**Model:**

**Stock No: KWBF750A**

**Serial No:**

Centrifugal Blower. Impeller diameter: 18 in. Baldor industrial motor, S/N: F0705144265. 15 hp, 3450 rpm, 208-230/460 V, 37-35/17.5 amps, 60 Hz, 3 phase. Frame: 215T. Code: 6206. Shaft diameter: 1- 3/8 in. Overall dimensions: 2 ft. L x 1 ft. 6 in. W x 1 ft. 4 in. H.



