

## Steel FAB Compressed Air Receiver – 1000 Gallons

Mfg: Steel FAB

Model:

Stock No: HNDC433

Serial No:

Steel FAB Compressed Air Receiver. Natl. BD. 171299. Part no. 1858.1234560. Approximate capacity: 1000 gallons. Straight wall: 11ft. 7-1/2 in. x 41 in. dia. MAWP 137 psi at 450°F. MDMT: -20°F at 137 PSI. HD: .274. SH: .313. Access door: 16 in. x 12-1/2 in. (2) 6-1/2 in., flanged with (8), 3/4 in. bolt size. (2) 1-3/4 in. screw fitting. (1) 3-1/4 in. threaded. (2) 2-1/2 in. Overall dimensions: 15 ft. 6-1/2 in. L x 6 ft. 5 in. W x 5 ft. 6-1/4 in. H.(ACN65).



