

**ITT Bell & Gossett 1540 Centrifugal Pump - 40 HP**

**Mfg: ITT B&G**

**Model: 5G 11.125 BF**

**Stock No.: JDWW100.**

**Serial No.:**

(11) Used ITT Bell & Gossett 1510 Series Centrifugal Pumps. Model: 5G 11.125 BF. Rated capacity for new pump is 682 gpm with required horsepower. Maximum working pressure: 175 psi. U.S. Electric Motor, 40 hp. Inlets: (1) 6 in. dia. flanged suction port. Outlets: (1) 5 in. dia. flanged discharge port. Overall dimensions: 6 ft. 1 in. L x 3 ft. 8-1/2 in. W x 4 ft. 2 in. H.





